

FAURE HERMAN

BP 20154 - 72406 LA FERTE BERNARD - MADE IN FRANCE

Equipment Type
 S/N Tag Year
 Op. pressure min/Max(Ps)
 Flowrange min/Max
 Testing pressure(Pt) Prove date
 T°min/Max(Ts) weight
 Danger group DN



STI	Nội Dung	xuất/ Xuất xứ																														
	<p>Faure Herman's Items</p> <p>3 Item Code: SEM_TZN</p> <p>Description: Cartridge TZN STD 100-300</p> <p>Part number:</p> <p>SEM_TZN STD 100-300</p> <p>SEM_TZN STD-H2-T-H-1-B-J-J-03-1-A</p> <table border="1"> <thead> <tr> <th>Selection</th> <th>Code</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>TZN Type</td> <td>STD</td> <td>Standard</td> </tr> <tr> <td>TZN Model / Size</td> <td>H2</td> <td>100-300 / 4"</td> </tr> <tr> <td>Rotor / Internal material</td> <td>T</td> <td>Titanium / Stainless Steel</td> </tr> <tr> <td>Type of fluid</td> <td>H</td> <td>Hydrocarbons</td> </tr> <tr> <td>Nb of calibration product(s)</td> <td>1</td> <td>1</td> </tr> <tr> <td>Number of points x Run(s)</td> <td>B</td> <td>6x3</td> </tr> <tr> <td>Minimum viscosity (cSt)</td> <td>J</td> <td>5 < V < 10</td> </tr> <tr> <td>Maximum viscosity (cSt)</td> <td>J</td> <td>5 < V < 10</td> </tr> <tr> <td>Accuracy / Repeatability</td> <td>3</td> <td>± 0.15% / 0.04% (± 0.02 %)</td> </tr> </tbody> </table>	Selection	Code	Description	TZN Type	STD	Standard	TZN Model / Size	H2	100-300 / 4"	Rotor / Internal material	T	Titanium / Stainless Steel	Type of fluid	H	Hydrocarbons	Nb of calibration product(s)	1	1	Number of points x Run(s)	B	6x3	Minimum viscosity (cSt)	J	5 < V < 10	Maximum viscosity (cSt)	J	5 < V < 10	Accuracy / Repeatability	3	± 0.15% / 0.04% (± 0.02 %)	<p>Faure Herman/ France</p>
Selection	Code	Description																														
TZN Type	STD	Standard																														
TZN Model / Size	H2	100-300 / 4"																														
Rotor / Internal material	T	Titanium / Stainless Steel																														
Type of fluid	H	Hydrocarbons																														
Nb of calibration product(s)	1	1																														
Number of points x Run(s)	B	6x3																														
Minimum viscosity (cSt)	J	5 < V < 10																														
Maximum viscosity (cSt)	J	5 < V < 10																														
Accuracy / Repeatability	3	± 0.15% / 0.04% (± 0.02 %)																														

